

50mm Diameter, Red Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#52-529** 3-5 DAYS



1



A\$63.20

ADD TO CART

Qty 1-24

A\$63.20

Qty 25+

A\$55.68

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00

Angle of Incidence (°):
0

Cut-On Wavelength (nm):
605.00

Substrate: 
Operating Temperature (°C): <100
Coating: Additive Color
Color: Red
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Cut-On Wavelength Tolerance (µm): 0.012
Coating Specification: T_{avg} <1.0% @ 390 - 570nm, T_{avg} >85% @ 620 - 750nm T_{abs} <2.0% @ 415 - 550nm, T_{abs} >80% @ 630 - 750nm

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant