

TECHSPEC[®] 50mm, Uncoated, N-BK7 High Tolerance RA Prism



N-BK7 High Tolerance Right Angle Prisms

Stock #49-007 3-5 DAYS



1



A\$353.60

ADD TO CART

Qty 1-5

A\$353.60

Qty 6+

A\$283.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (arcsec):
±15

Coating:
Uncoated

Substrate: ☐
[N-BK7](#)

Surface Quality:

40-20
Type: Right Angle Prism
Dimensional Tolerance (mm): +0/-0.1
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 70.70
Length of Legs (mm): 50.00
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 350 - 2200
Surface Flatness (P-V): $\lambda/8$
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View