

## 560nm CWL, 10nm FWHM, 50mm Mounted Diameter



Stock #67-900 3-5 DAYS

- 1 +

A\$710.40

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-9                       |
| A\$710.40                     |
| Qty 10+                       |
| A\$638.40                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
50.00 +0.00/-0.25

Angle of Incidence (°):  
0

Optical Density OD (Average):  
≥4.0

Clear Aperture CA (mm):

|                                                           |
|-----------------------------------------------------------|
| 45.0                                                      |
| <b>Center Wavelength CWL (nm):</b><br>560.00 +3.0/-1.0    |
| <b>Center Wavelength CWL Tolerance (nm):</b><br>+3.0/-1.0 |
| <b>Full Width-Half Max FWHM (nm):</b><br>10.00 ±2         |
| <b>Full Width-Half Max FWHM Tolerance (nm):</b><br>±2     |
| <b>Minimum Transmission (%):</b><br>>55                   |
| <b>Operating Temperature (°C):</b><br>-50 to +70          |
| <b>Coating:</b><br>Traditional Coated                     |
| <b>Surface Quality:</b><br>80-50                          |
| <b>Type:</b><br>Bandpass Filter                           |
| <b>Typical Applications:</b><br>TRITC Excitation          |
| <b>Blocking Wavelength Range (nm):</b><br>200 - Far IR    |
| <b>Construction:</b><br>Mounted in Black Anodized Ring    |
| <b>Mount Thickness (mm):</b><br>5.9 ±0.1                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |