

600 Grooves/mm, 25mm Sq, UV Transmission Grating Beamsplitter



Stock #85-292 3-5 DAYS

- 1 + **A\$372.00**

ADD TO CART

Qty 1-9
A\$372.00
Qty 10+
A\$335.20
Volume Pricing
Request Quote

Get Product Downloads



Groove Density (grooves/mm):
600

Wavelength Range (nm):
250 - 600

Blaze Angle (°):
22.0

Dimensions (mm): 25.00 x25.00
Construction: Blazed Grating
Length (mm): 25.00
Substrate:  Fused Silica (Corning 7980)
Thickness (mm): 2.00 ±0.5
Type: Transmission Diffraction Grating
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View