

64mm Dia x 78mm FL Cold Mirror Coated, Ellipsoidal Reflector



Precision Ellipsoidal Reflectors

Stock **#90-973** [CONTACT US](#)



1



A\$436.80

ADD TO CART

Qty 1-10

A\$436.80

Qty 11+

A\$381.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate: 

Coating:
Cold Mirror, 0°

Coating Type:
Metal

Center Hole Diameter (mm):

18.0
Height (mm): 44.0
Inner Diameter (mm): 60
Outer Diameter (mm): 64.00 +0.0/-0.5
Type: Specialty Mirror
Distance to Focal Point f₁ (mm) : 11
Distance to Focal Point f₂ (mm): 78

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
