

TECHSPEC® 8" Diameter x 40" FL Uncoated, Parabolic Mirror



Stock #32-073-000 3-5 DAYS

⊖ 1 ⊕ **A\$1,348.80**

ADD TO CART

Qty 1-2
A\$1,348.80
Qty 3+
A\$1,147.20
Volume Pricing
Request Quote

Get Product Downloads

Substrate: □
[BOROFLOAT®](#)[SUPREMAX®](#)

Focal Length Tolerance (%):
±1.5

Surface Quality:
60-40

Surface Accuracy:
λ/8

Diameter (inches): 8.0 +0.06/-0
Diameter (mm): 203.20 +1.5/-0
Effective Focal Length EFL (inches): 40.0
Effective Focal Length EFL (mm): 1,016.00
Radius of Curvature (mm): 2,032.00
Aperture (f/#): f/5
Coating: Uncoated
Coating Type: Uncoated
Back Surface: Ground
Clear Aperture CA (mm): 183
Edge Thickness ET (inches): 1.37
Edge Thickness ET (mm): 34.80
Type: Parabolic Mirror

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View