

TECHSPEC[®] 9mm Dia. x -18mm FL, Uncoated, Double-Concave Lens



Stock **#48-682** 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$45.60

ADD TO CART

Qty 1-9
A\$45.60
Qty 10+
A\$41.20
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.00 +0.0/-0.025

Effective Focal Length EFL (mm):
-18.00

Substrate: N-BK7
f#: 2.00
Numerical Aperture NA: 0.25
Coating: Uncoated
Type: Double-Concave Lens
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -18.49
Bevel: Protective bevel as needed
Center Thickness CT (mm): 1.50
Center Thickness Tolerance (mm): ±0.05
Centering (arcmin): <1
Clear Aperture CA (mm): 8.1
Edge Thickness ET (mm): 2.45
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁=R₂ (mm): -18.86
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View