

Apo-Componon f/4.0, 45mm Focal Length



Stock #63-055

CONTACT US

-

1

+

A\$2,032.00

ADD TO CART

Qty 1+
A\$2,032.00

Volume Pricing
Request Quote

Get Product Downloads

Iris Option:

Fixed

Maximum Diameter (mm):

47.00

Maximum Image Circle (mm):

43.30

Type:

Fixed Focal Length Lens

Focal Length FL (mm):

45.00

Maximum Sensor Format: 35mm (43.3mm Image Circle)
Mount: Adapter Required
Aperture (f/#): f/4
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant