

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Basler ace GigE Cameras](#)

[See all 66 Products in Family](#)

Basler ace acA2040-25gm Monochrome GigE Camera



Basler ace GigE Cameras



Stock **#87-104** 3-5 DAYS

[Similar Cameras](#)

- 1 +

A\$3,566.40

ADD TO CART

Qty 1+
A\$3,566.40

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Monochrome Camera

Manufacturer:

Basler
Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-517
Camera Family: ace
Model Number: acA2040-25gm
Imaging Sensor: CMOSIS CMV4000
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1"
Resolution (MegaPixels): 4.20
Pixels (H x V): 2,048 x2,048
Pixel Size, H x V (µm): 5.5 x5.5
Sensing Area, H x V (mm): 11.26 x11.26
Frame Rate (fps): 25.00
Pixel Depth: 12 bit
Exposure Time: Freely Programmable
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #68-466 Europe: #68-466 Japan: #68-466 Korea: #68-466 China: #68-466
Power Consumption (W): 2.6 (12VDC External Power Supply) 3.1 (PoE)
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 1 general purpose I/O (GPIO) line
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 42 x29 x29 (excludes connectors and lens mount)
Weight (g): 90
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 58.7
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: GigE Vision
Operating System: Software Driver: Windows, Linux - 32 and 64 bit

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View

