

TECHSPEC® Elliptical Mirror 47.63mm Minor Axis Uncoated



Stock **#32-097** 3-5 DAYS

- 1 + **A\$272.00**

ADD TO CART

Qty 1-5
A\$272.00
Qty 6+
A\$217.60
Volume Pricing
Request Quote

Get Product Downloads



Minor Axis (mm):
47.63

Major Axis (mm):
67.36

Surface Flatness (P-V):
λ/8

Substrate:

[BOROFLOAT®](#)

Surface Quality:
60-40

Dimensional Tolerance (mm):
±0.38

Dimensional Tolerance (inches):
±0.015

Coating:
Uncoated

Coating Type:
Uncoated

Clear Aperture CA (mm):
42.88 (Minor Axis)
60.63 (Major Axis)

Note:
Flatness specification is Peak to Valley

Thickness (mm):
11.68

Thickness Tolerance (inches):
±0.040

Thickness Tolerance (mm):
±1.02

Type:
Flat Mirror

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 219:
[Compliant](#)

Certificate of Conformance:
[View](#)