

Germanium, 12.7mm, Uncoated, ISP Optics IR Right Angle Prism | GE-RP-12

See More by [ISP Optics](#)



Infrared (IR) Right Angle Prisms

Stock **#25-040** 3-5 DAYS

1

A\$1,888.00

ADD TO CART

Qty 1+

A\$1,888.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:

Uncoated

Substrate: ☐

Germanium (Ge)

Surface Quality:

60-40

Type:

Right Angle Prism

Dimensional Tolerance (mm): ±0.25
Angle Tolerance (arcmin): ±10
Clear Aperture (%): 85.00
Length of Hypotenuse (mm): 18.00
Length of Legs (mm): 12.70
Image Orientation: Left-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 2000 - 14000
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 2λ
Model Number: GE-RP-12

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View