

M39 x 0.5 Mounted IR Cut-Off Filter



Stock #49-803 3-5 DAYS

-

1

+

A\$292.80

ADD TO CART

Qty 1-9
A\$292.80
Qty 10+
A\$269.28
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
33.8

Filter Thread:
M39 x 0.50

Cut-Off Wavelength (nm):
750.00

Glass/Filter Number:
[SCHOTT KG3](#)

Index of Refraction n_d: 1.52
Note: AR Coating: Both Surfaces Multilayer Broadband AR
Outer Diameter (mm): 40.5
Substrate: Schott KG-3
Substrate Thickness (mm): 2.0
Surface Quality: 60-40
Thickness with Mount (mm): 6.4
Type: Mounted Imaging Filter
Wavelength Range (μm): 0.3 - 2.7
Wavelength Range (nm): 300 - 2700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant