

M62.0 x 0.75 Mounted UV/VIS Cut-Off, IR Pass Filter (R-72)



Stock #64-888 3-5 DAYS

- 1 + **A\$228.80**

ADD TO CART

Qty 1-9
A\$228.80
Qty 10+
A\$210.56
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
56.8

Coating Specification:
R_{avg} ≤1.75% @400 - 700nm

Filter Thread:
M62 x0.75

Cut-Off Wavelength (nm):
2,750.00

Cut-On Wavelength (nm): 720.00
Glass/Filter Number: R-72
Index of Refraction n_d: 1.55
Mount Thickness (mm): 7.4 ±0.1
Mount Thickness Including Threads (mm): 8.0
Note: AR Coating: Both Surfaces Single Layer MgF ₂
Outer Diameter (mm): 64.5
Substrate:  Hoya R-72
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness with Mount (mm): 5.0
Type: Mounted Imaging Filter

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View