

Mounted M46 x 0.75 Threaded - Blue Filter



Stock #46-571 3-5 DAYS

- 1 +

A\$90.40

ADD TO CART

Qty 1-9
A\$90.40
Qty 10+
A\$84.00
Volume Pricing
Request Quote

Get Product Downloads

Clear Aperture CA (mm):
41.5

Filter Thread:
M46 x 0.75

Color:
Blue

Cut-Off Wavelength (nm):
480.00

Cut-On Wavelength (nm): 395.00
Glass/Filter Number: B-440
Index of Refraction n_d: 1.55
Note: AR Coating: MgF ₂
Outer Diameter (mm): 48.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.0
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.0
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya B-440 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View