

Mounted M52 x 0.75 Threaded - Blue Filter



Stock **#54-776** CLEARANCE 3-5 DAYS

-

1

+

A\$39.92

ADD TO CART

Qty 1+

A\$39.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):
48.0

Filter Thread:
M52 x0.75

Color:
Blue

Cut-Off Wavelength (nm):
480.00

Cut-On Wavelength (nm):
395.00

Glass/Filter Number: B-440
Index of Refraction n_d: 1.55
Note: AR Coating: MgF ₂
Outer Diameter (mm): 54.0
Substrate: ☐ Colored Glass
Substrate Thickness (mm): 2.5
Surface Quality: 80-50
Thickness of Compatible Optics (mm): 2.5
Thickness with Mount (mm): 5.00
Type: Mounted Imaging Filter
Type of Filter: Hoya B-440 or equivalent
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View