

## Mounted M58 x 0.75 Threaded - Blue Filter



Stock #54-777 3-5 DAYS

- 1 +

A\$90.40

ADD TO CART

Qty 1-9

A\$90.40

Qty 10+

A\$84.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture CA (mm):  
54.0

Filter Thread:  
M58 x 0.75

Color:  
Blue

Cut-Off Wavelength (nm):  
480.00

|                                                             |
|-------------------------------------------------------------|
| <b>Cut-On Wavelength (nm):</b><br>395.00                    |
| <b>Glass/Filter Number:</b><br>B-440                        |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.55        |
| <b>Note:</b><br>AR Coating: MgF <sub>2</sub>                |
| <b>Outer Diameter (mm):</b><br>60.0                         |
| <b>Substrate:</b> <input type="checkbox"/><br>Colored Glass |
| <b>Substrate Thickness (mm):</b><br>2.5                     |
| <b>Surface Quality:</b><br>80-50                            |
| <b>Thickness of Compatible Optics (mm):</b><br>2.5          |
| <b>Thickness with Mount (mm):</b><br>5.00                   |
| <b>Type:</b><br>Mounted Imaging Filter                      |
| <b>Type of Filter:</b><br>Hoya B-440 or equivalent          |
| <b>Wavelength Range (nm):</b><br>400 - 700                  |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |