


SCHOTT OG515, 50mm Sq., 3mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-495** 3-5 DAYS

- 1 +

A\$124.00

ADD TO CART

Qty 1-10
A\$124.00
Qty 11+
A\$121.60
Volume Pricing
Request Quote

Get Product Downloads
Dimensions (mm): 50.0 x 50.0
Cut-On Wavelength (nm): 515.00 ±6
Density (g/cm³):

2.56
Glass/Filter Number: SCHOTT OG515
Length (mm): 50.00
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 580
Index of Refraction n_d : 1.51
Spectral Transmittance t_p (%): 93
Stopband Limit λ_s (nm): 440
Surface Quality: 60-40
Transformation Temperature (°C): 509
Thickness (mm): 3.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View