

TECHSPEC[®] VIS Coated, C-Mounted Non-Polarizing Cube Beamsplitter



C-Mounted Cube Beamsplitters

Stock #49-682 3-5 DAYS



1



A\$633.60

ADD TO CART

Qty 1-4

A\$633.60

Qty 5+

A\$497.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle Tolerance (arcmin):

±2

Coating:

Faces: Multi-Layer Anti-Reflection for Visible Region

Construction:

Cube

Dimensions (mm):

38.0 x 38.0 x 50.0
Extension Length (mm): 38.0
Housing: Black Anodized Aluminum
Mount: C-Mount Enclosure
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Quality: 40-20
Thread Type: C-Mount (1" x 32 TPI)
Type: Non-Polarizing Beamsplitter
Type of Optics: Non-Polarizing Cube Beamsplitter, V/S Coating
Wavelength Range (nm): 430 - 670
Beamsplitter Included: #47-009
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.25

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View