



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES




492841NK
TUE DEC 16 2008 UNITS ARE μm .
FIELD :
RMS RADIUS : 49.704
GD RADIUS : 139.022
SCALE BAR : 400

REFERENCE : CHIEF RAY

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

492841NK
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 474.1195 μm
DIFFRACTION LIMITED RANGE: 9.296 μm
PUPIL ZONE: 0.0000


EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM



492841NK
TUE DEC 16 2008
MAXIMUM SCALE: $\pm 500.000 \mu\text{m}$.
0.486 0.588 0.656
SURFACE: IMAGE

EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM

492841NK
TUE DEC 16 2008
DATA FOR 0.4250 TO 0.6750 μm .
SURFACE: IMAGE



EDMUND OPTICS
HTTP://WWW.EDMUNDOPTICS.COM