



TECHSPEC® Achromatic Lenses

Edmund Optics Inc.

USA | UK | France | Germany | Japan | Singapore | China | Korea | Italy

TECHSPEC® ACHROMATIC LENSES





49792 TUE DEC 16 2008 UNITS ARE μM. FIELD : 50.208 RMS RADIUS : 126.496 SCALE BAR : 400	SPOT DIAGRAM	EDMUND OPTICS HTTP://WWW.EDMONDOPTICS.COM
REFERENCE : CHIEF RAY		

49792
TUE DEC 16 2008
MAXIMUM FOCAL SHIFT RANGE: 394.6199 μM
DIFFRACTION LIMITED RANGE: 9.445 μM
PUPIL ZONE: 0.0000

CHROMATIC FOCAL SHIFT

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)



49792 TUE DEC 16 2008 MAXIMUM SCALE: ± 500.000 μM. 0.486 0.588 0.656	TRANSVERSE RAY FAN PLOT	EDMUND OPTICS HTTP://WWW.EDMONDOPTICS.COM
SURFACE: IMAGE		

49792
TUE DEC 16 2008
DATA FOR 0.4000 TO 1.0000 μM.
SURFACE: IMAGE

EDMUND OPTICS
[HTTP://WWW.EDMONDOPTICS.COM](http://www.edmundoptics.com)