NOTES:

1. SUBSTRATE MATERIAL: N-BK7

2. ROHS COMPLIANT


3. SURFACE \$1 TO BE PARALLEL WITH SURFACE \$2 TO WITHIN ≤ 3 ARCMIN


4. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 20% R ±5% @ 550nm 80% T ±5% @ 550nm

S2: AR R(avg) ≤1%, R(abs) ≤2% @ 700 - 1100nm

5. EDGES CUT





FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

 \square

	,		_			Edmund Optic	'C®
REV. A	S1	S2					טי ו
SHAPE	PLANO	PLANO		1			
ANGLE OF INCIDENCE	45°	45°	THIRD ANGLE		TITLE	75 x 75mm, 20 R/80 T, PLATE BEAMSPLITTER	2
SURFACE QUALITY	60-40	60-40					
SURFACE FLATNESS	1λ PER 25mm	1λ PER 25mm	ALL DIMS IN	mm	DWG NO	68380	Sheet 1 Of 1