

NOTES:



1. SUBSTRATE MATERIAL: BOROFLOAT®

2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: R(AVG) >85% @ 400 - 700nm  
R(AVG) >90% @ 400 - 2000nm  
S2: NONE

3. FINE GRIND SURFACE



4. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2
TYPE	PLANO	PLANO
CLEAR APERTURE (mm)	34.34 x 24.28	N/A
SURFACE QUALITY	60-40	N/A
SURFACE FLATNESS	λ/8	N/A
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			
THIRD ANGLE PROJECTION 		TITLE	26.97mm, MINOR AXIS PROTECTED ALUM. ELLIPTICAL MIRROR
ALL DIMS IN	mm	DWG NO	30837
			SHEET 1 OF 1