NOTES:

1. SUBSTRATE MATERIAL: BOROFLOAT©


2. COATING (APPLY ACROSS CLEAR APERTURE)


S1: R(avg) <0.5% @ 425 - 675nm HYDROPHOBIC COATING - REPELS WATER, OIL AND DEBRIS


S2:NONE

3. FINE GRIND SURFACE

4. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

| | \$1 | \$2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 80 - 50 | 80 - 50 |
| CLEAR APERTURE | Ø22.50 | Ø22.50 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

| | | | Edmund Optics® | | |
|---|------------------------|----|----------------|---|-----------------|
| | THIRD ANGLE PROJECTION | | TITLE | WINDOW BORO HYDRO & OLEOPHOBIC 25MM TS | |
|) | ALL DIMS IN | mm | DWG NO | 34526 | SHEET 1 OF 1 |