

NOTES:

1. SUBSTRATE MATERIAL:
NITROCELLULOSE

2. COATING (APPLY ACROSS COATING APERTURE)

S1: DIELECTRIC


33% R @ 400 - 700nm @ 45° AOI

67% T @ 400 - 700nm @ 45° AOI


R/T TOLERANCE: ±3%

S2: NONE

3. ROHS : EXEMPT



SECTION A-A



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| REV.A. | S1 | S2 |
|-----------------|----------------------|----------------------|
| SHAPE | PLANO | PLANO |
| SURFACE QUALITY | 40-20 | 40-20 |
| CLEAR APERTURE | Ø101.60 | Ø101.60 |
| BEVEL | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION

ALL DIMS IN

mm

EO® **Edmund Optics**®

TITLE

BS PELLICLE 4in DIA 33R/67T

DWG NO

39492

SHEET
1 OF 1