



NOTES:

- 1. SUBSTRATE:
B270
- 2. GROOVE ANGLE: 36.9°
- 3. WAVELENGTH: VIS
WAVELENGTH RANGE (nm): 400 - 700
- 4. GROOVE DENSITY (grooves/mm): 1200
- 5. ARROW ON EDGE DEPICTS BLAZE DIRECTION.



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

<div><div>EO[®]</div><div>Edmund Optics[®]</div></div>			
THIRD ANGLE PROJECTION 		TITLE	1200 Grooves, 50mm Sq, 36.9° Groove Angle Grating
ALL DIMS IN	mm	DWG NO	49586
			SHEET 1 OF 1