






FOCAL LENGTH (EFL): 88,9 ± 0,89
BACK FOCAL LENGTH (BFL): 83,96

1 BLACKENED SURFACE


SURFACE A			SURFACE B		SURFACE C			
Øe 24,4			Øe 24,4		Øe 24,4			
			CEMENT: NOA 61 OR EQUIVALENT					
PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics® TITLE 25,4mm Dia, x 88,9mm FL, VIS 0, Inked, Achromatic Lens			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY								
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING			ALL DIMS IN: mm		DWG NO 49782INK		SHEET SIZE A4	SHEET 1 OF 3
INDICATIONS IN ACCORDANCE WITH ISO 10110								



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI



LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 56,98±0,057 CX Øe 24,4 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-BaK1 573/576	R 40,06±0,04 CX Øe 24,4 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®				
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm			TITLE 25,4mm Dia, x 88,9mm FL, VIS 0, Inked, Achromatic Lens				
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY			ALL DIMS IN: mm						
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING									
INDICATIONS IN ACCORDANCE WITH ISO 10110			DWG NO 49782INK			SHEET SIZE A4		SHEET 2 OF 3	



- 1 AR COATING: VIS 0°
R(AVG) ≤ 0,4% FROM 425-675nm @ 0° AOI

LEFT SURFACE	MATERIAL	RIGHT SURFACE
R 40,06±0,04 CV Øe 24,4 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -	GLASS N-SF8 689/312	R 162,82±0,163 CX Øe 24,4 3/ 3 (0,5) λ=632,8 nm 4/ - 5/ 40 - 20 (MIL-PRF-13830B) 6/ -

PROTECTIVE CHAMFERS AS NEEDED			FIRST ANGLE PROJECTION 		 Edmund Optics®			
ROHS: COMPLIANT	SCALE: NONE	λ = 587,6nm						
SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE. DIMENSIONS ARE FOR REFERENCE ONLY					TITLE	25,4mm Dia, x 88,9mm FL, VIS 0, Inked, Achromatic Lens		
FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING					DWG NO	49782INK	SHEET SIZE A4	SHEET 3 OF 3
INDICATIONS IN ACCORDANCE WITH ISO 10110			ALL DIMS IN:	mm				