





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



	VALUE
WAVELENGTH (nm)	405
OUTPUT POWER	50
COLOR	VIOLET
LASER CLASS	CLASS IIIB
OPERATING TEMPERATURE (°C)	+15 to +30
OPERATING VOLTAGE (V)	5.0
SPATIAL MODE	FIBER-COUPLED
LASER TYPE	DIODE
CONNECTOR	SMA
LENGTH OF FIBER (m)	1

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

EO® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	50mW, 405nm Fiber-Coupled Laser Module	
ALL DIMS IN	mm	DWG NO	19477	SHEET 1 OF 1