

1/4-20 Bumper (Package of 4), Sorbothane Bumpers



Stock #55-244 **8 In Stock**

- 1 + A\$77²⁰

ADD TO CART

Volume Pricing

| | |
|------------|-------------------------------|
| Qty 1-2 | A\$77.20 each |
| Qty 3+ | A\$68.48 each |
| Need More? | Request Quote |

Product Downloads

General

English **Type:**
1/4-20 **Note:**

Physical & Mechanical Properties

25.40 **Thickness (mm):**

| | |
|---------------------------------|------------------------------------|
| Sorbothane | Construction: |
| 38.10 | Diameter (mm): |
| 30-65 / bumper | Load Capacity (lbs): |
| Threading & Mounting | |
| 12.7 | Thread Length (mm): |
| Regulatory Compliance | |
| Compliant | RoHS 2015: |
| View | Certificate of Conformance: |

Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.

;