

## 1/4-20 Bumper (Package of 4), Sorbothane Bumpers



Stock #55-244 **10 In Stock**

- 1 + A\$77<sup>20</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-2	A\$77.20 each
Qty 3+	A\$68.48 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English **Type:**  
1/4-20 **Note:**

### Physical & Mechanical Properties

25.40 **Thickness (mm):**

Sorbothane	<b>Construction:</b>
38.10	<b>Diameter (mm):</b>
30-65 / bumper	<b>Load Capacity (lbs):</b>
<b>Threading &amp; Mounting</b>	
12.7	<b>Thread Length (mm):</b>
<b>Regulatory Compliance</b>	
<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Absorb and Dissipate Vibration
- Stabilize Equipment up to 152lbs
- English, Metric, or Universal Styles

Sorbothane® Mounts absorb (57% absorption efficiency) and dissipate energy (70% specific damping). The mounts reduce vibration to other components by isolating the vibrations within the material while absorbing multi-directional forces. These hemisphere mounts can stabilize equipment weighing up to 38 pounds (hemisphere mounts), 65 pounds (1/4-20 male bumper mounts), or 29.4 kg (M6 male bumper mounts). Sorbothane® Mounts measure 50mm dia. (top) x 26mm thick. The top side of the hemisphere is tacky, while the other side is felt. 1/4-20 or M6 male bumper mounts measure 38.1mm dia. x 25.4mm thick. The threaded screw measures 12mm long. All models have a hardness durometer value of 70. Each package contains 4 mounts.

;