

[See all 12 Products in Family](#)

## (0-3" Range), 0.0001", Mechanical Outside Micrometer, Set of 3

See More by [Mitutoyo](#)



Stock #78-305 **1 In Stock**

⊖ 1 ⊕ A\$912<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	A\$912.00 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

±0.001

**Accuracy (inches):**

### General

0 - 3 inches

**Range:**

103-922

**Model Number:**

**Contents of Kit:**

Outside Micrometer with Friction Thimble: 0-1"  
Outside Micrometer with Friction Thimble: 1-2"

## Physical & Mechanical Properties

**Graduation (inches):**  
0.0001

## Regulatory Compliance

**Certificate of Conformance:**  
[View](#)

## Product Details

- Available as Standard, Blade Micrometer, or with Interchangeable Anvils
- Measurement Ranges from 0 – 6"
- Baked Enamel Finish on Frame for Durability

Mitutoyo Mechanical Micrometers provide quick and accurate external measurements and are available in several form factors to best suit the application. The Uni-Mke Micrometer features interchangeable anvils ranging from 0-1" for measuring tube thickness, rivet head heights, and shoulder-edge distances. The non-rotating spindle type blade micrometer utilizes a blade anvil and spindle to reach difficult to measure areas and reduce torsion on softer parts, making it ideal for grooves and keyways. Mitutoyo Mechanical Micrometers feature a ratchet stop or friction thimble to provide uniform pressure on a workpiece for precise, repeatable measurements. These micrometers are designed with a baked enamel finish and carbide facing on the spindles and anvils for enhanced durability and longer lifespan.