

0 - 4 OD, ISO-21550 Dynamic Range Film



Stock **#58-942** **2 In Stock**

-

1

+

A\$336^{.00}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$336.00 each
Qty 5+	A\$320.64 each
Need More?	Request Quote

Product Downloads

General

No

NIST Certification:

Physical & Mechanical Properties

75.00

Length (mm):

~28 x 19

Pattern Size (mm):

35.00

Width (mm):

4.5 x 4.5	Patch Size (mm):
Optical Properties	
Transmissive Photo Paper	Substrate:
0 - 4	Optical Density OD (Average):

Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Used to Determine Optical Density Range of Transmission Scanners and Imaging Systems
- The dynamic range 35mm film can be used to determine the optical density range of a transmission scanner or other transmission imaging systems. It is a perforated 35mm filmstrip with gray scale patches.

Technical Information

Patch #		#58-942 0-4 Visual Weighted OD																								
1		0.107																								
2		0.107																								
3		0.125																								
4		0.217																								
5		0.426																								
6		0.718																								
7		1.050																								
8		1.418																								
9		1.869																								
10		2.312																								
11		2.496																								
12		2.672																								
13		2.922																								
14		3.160																								
15		3.262																								
16		3.307																								
17		3.422																								
18		3.540																								
19		3.641																								
20		3.690																								
21		3.759																								
22		3.842																								
23		3.900																								
24		4.028																								
<table><tr><td>24</td><td>22</td><td>19</td><td>15</td><td>11</td><td>7</td></tr><tr><td>23</td><td>20</td><td>16</td><td>12</td><td>8</td><td>4</td></tr><tr><td>21</td><td>17</td><td>13</td><td>9</td><td>5</td><td>2</td></tr><tr><td>18</td><td>14</td><td>10</td><td>6</td><td>3</td><td>1</td></tr></table>			24	22	19	15	11	7	23	20	16	12	8	4	21	17	13	9	5	2	18	14	10	6	3	1
24	22	19	15	11	7																					
23	20	16	12	8	4																					
21	17	13	9	5	2																					
18	14	10	6	3	1																					

