


0.04 - 1.0 OD, 50mm, Apodizing Filter Reverse Bull's Eye



Reverse Bullseye Filter

Stock **#64-391** 3-5 DAYS

- 1 + **A\$606.40**

ADD TO CART

Qty 1-10

A\$606.40

Qty 11+

A\$544.32

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.20

Optical Density OD (Average):
0.04 - 1.0

Substrate:
[B270](#)

Type of Filter: Reverse Bull's Eye
Coating: Variable
Surface Quality: 60-40
Thickness (mm): 1.50
Thickness Tolerance (mm): ±0.10
Type: Apodizing Filter
Linearity (%): ±5 of Optical Density
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View