

0.125" Travel, X Axis, Micro Series with Covered Rails (A)



Stock #56-416 3-5 DAYS

-

1

+

A\$452.80

ADD TO CART

Qty 1+

A\$452.80

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
Fine Screw (80 Pitch)

Drive Orientation:
Center Drive

Type: English
Stage Size (mm): 14.2 x 26.2
Travel (mm): 3.1
Travel (inches): 0.125
Center Hole: 0.155" (3.94mm) thru with 8-32 tap
Construction: Aluminum Body, Stainless Steel Rails
Load Capacity, Normal (kg): 0.25
Note: With Covered Rails
Stage Size (inches): 0.56 x 1.03
Straight Line Accuracy (µm): 1.5
Weight (g): 4
Wobble (mrad): 0.01

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
