

0.3 - 2.5µm, 30W, Volume Absorber, Wireless Power & Energy Detector



0.3 - 2.5µm, 30W, Volume Absorber, Wireless Power & Energy Detector

Stock #17-211 CLEARANCE 3-5 DAYS

1 **A\$4,473.52**

ADD TO CART

Qty 1+
A\$4,473.52

Volume Pricing
Request Quote

Get Product Downloads

Dimensions (mm):
80.6 x 50 x 61.3

Weight (g):
210

Weight (kg):
0.21

Type of Sensor:
Volume Absorber

Active Area (mm):
18

Computer Interface: Bluetooth®
Maximum Incident Beam Power (mW): 30,000
Cooling Method: Heatsink
Maximum Incident Beam Power (W): 30
Maximum Incident Power Density (W/cm²): 700
Maximum Incident Power Density (kW/cm²): 0.7
Maximum Incident Energy Density (J/cm²): 6
Noise Level: 2 mW
Compatible Meters: Not Required
Wavelength Range (nm): 300 - 2500
Wavelength Range (µm): 0.3 - 2.5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
