

TECHSPEC[®] 0.3 OD 50mm Square, Reflective ND Filter



Stock #43-813 3-5 DAYS

-

1

+

A\$115.20

ADD TO CART

Qty 1-5

A\$115.20

Qty 6+

A\$92.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Angle of Incidence (°):
0

Optical Density OD (Average):
0.3

Substrate: Float Glass
Length (mm): 50.00
Coating: Surface 1: Inconel
Reflection (%): 21.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%): 50.00
Type: Neutral Density Filter
Width (mm): 50.00
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%): 80
Neutrality: ±5% of Optical Density
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant