

0.3 OD M37 x 0.50, Machine Vision Absorptive ND Filter



Stock #21-563

3-5 DAYS

-

1

+

A\$100.00

ADD TO CART

Qty 1-9
A\$100.00
Qty 10+
A\$95.68
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
32.50

Filter Thread:
M37 x 0.50

Substrate:
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 50.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
