

0.3 OD M55.0 x 0.75, Mounted Absorptive ND Filter



Stock **#65-014** CLEARANCE 3-5 DAYS

-

1

+

A\$62.32

ADD TO CART

Qty 1+

A\$62.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
51.0

Filter Thread:
M55 x0.75

Substrate:
ND Filter Glass

Thickness with Mount (mm):
5.00

Surface Quality: 80-50
Transmission (%): 50
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 3.8 ±0.1
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 57.0 +0/-0.2
Mount Thickness Including Threads (mm): 6.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View