

0.5 OD, 25.4mm Dia., Reflective Neutral Density Filter



Stock #27-928 CLEARANCE 3-5 DAYS

-

1

+

A\$23.92

ADD TO CART

Qty 1+

A\$23.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):  
25.40 ±0.3

Optical Density OD (Average):  
0.5

Substrate: ☐  
Borosilicate

Coating:  
Metallic Based ND

Thickness (mm):  
1.00

|                                       |
|---------------------------------------|
| Thickness Tolerance (mm):<br>±0.25    |
| Transmission (%):<br>32.00            |
| Type:<br>Neutral Density Filter       |
| Parallelism (arcmin):<br>±3           |
| Dimensional Tolerance (mm):<br>±0.3   |
| Clear Aperture (%):<br>>90            |
| Optical Density Tolerance (%):<br>±10 |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br>Compliant                                  |
| Certificate of Conformance:<br><a href="#">View</a> |