

0.5 OD, 25mm Dia., IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock **#64-354** [CONTACT US](#)

-

1

+

A\$614.40

ADD TO CART

Qty 1-10

A\$614.40

Qty 11+

A\$551.84

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 ±0.2

Optical Density OD (Average):
0.5

Substrate: ☐
Germanium (Ge)

Coating:

Metallic Based ND
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 31.6
Transmission Tolerance (%): ±2.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 2000 - 14,000
Parallelism (arcmin): <10
Clear Aperture (%): 90
Wavelength Range (µm): 2 - 14
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant