

**TECHSPEC® 0.5 OD 25mm Diameter, Reflective ND Filter**



Stock **#30-934** CLEARANCE 3-5 DAYS

- 1 +

**A\$80.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| A\$80.00                      |
| Qty 6+                        |
| A\$64.00                      |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



Diameter (mm):  
25.00

Angle of Incidence (°):  
0

Optical Density OD (Average):  
0.5

|                                                                                                       |
|-------------------------------------------------------------------------------------------------------|
| <b>Substrate:</b> <div><div></div></div> <div>Float Glass</div>                                       |
| <b>Coating:</b> <div>Surface 1: Inconel</div>                                                         |
| <b>Reflection (%)</b> : <div>30.00</div>                                                              |
| <b>Surface Quality</b> : <div>80-50</div>                                                             |
| <b>Thickness (mm)</b> : <div>1.60 Nominal</div>                                                       |
| <b>Transmission (%)</b> : <div>32.00</div>                                                            |
| <b>Type</b> : <div>Neutral Density Filter</div>                                                       |
| <b>Blocking Wavelength Range (nm)</b> : <div>400 - 700</div>                                          |
| <b>Dimensional Tolerance (mm)</b> : <div>±0.5</div>                                                   |
| <b>Clear Aperture (%)</b> : <div>80</div>                                                             |
| <b>Neutrality</b> : <div>±5% of Optical Density</div>                                                 |
| <b>Note</b> : <div>Optical density values are average over specified blocking wavelength range.</div> |
| <b>Surface Flatness (P-V)</b> : <div>4 - 6λ</div>                                                     |

## Regulatory Compliance

|                                                    |
|----------------------------------------------------|
| <b>RoHS 2015:</b> <div>Compliant</div>             |
| <b>Certificate of Conformance:</b> <div>View</div> |
| <b>Reach 235:</b> <div>Compliant</div>             |