

## 0.5" Travel, 0.001" Grad. Mic. Drive F-Face



Drive Mechanisms

Stock #33-728 **1 In Stock**

⊖ 1 ⊕ A\$136<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-9	A\$136.00 each
Qty 10-24	A\$122.40 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

English **Type:**  
Mtutoyo **Manufacturer:**

### Physical & Mechanical Properties

0.5 **Travel (inches):**  
**Graduation (inches):**

0.001	
9.5	<b>Stem Diameter (mm):</b>
Plain/Flat	<b>Stem/Spindle:</b>
9.5	<b>Stem Length (mm):</b>
5	<b>Spindle Diameter (mm):</b>
15.5	<b>Min. Spindle Length (mm):</b>
13	<b>Max. Diameter (mm):</b>
62	<b>Overall Length (mm):</b>

## Hardware & Interface Connectivity

English Micrometer	<b>Type of Drive:</b>
--------------------	-----------------------

## Regulatory Compliance

<a href="#">Exempt</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>
<a href="#">Contains SVHC(s)</a>	<b>REACH 241:</b>

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
- Compatible with our [Ball Bearing Stages](#)

These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.

Please reference individual product descriptions to see which stages are compatible with each drive mechanism.