

0.5" Travel, 0.001" Grad. Mic. Drive F-Face



Drive Mechanisms

Stock **#33-728** 1 In Stock

-

1

+

A\$136⁰⁰

ADD TO CART

Volume Pricing	
Qty 1-9	A\$136.00 each
Qty 10-24	A\$122.40 each
Need More?	Request Quote

Product Downloads

General	
English	Type:
Mitutoyo	Manufacturer:
Physical & Mechanical Properties	
0.5	Travel (inches):
	Graduation (inches):

0.001	
	Stem Diameter (mm):
9.5	
	Stem/Spindle:
Plain/Flat	
	Stem Length (mm):
9.5	
	Spindle Diameter (mm):
5	
	Min. Spindle Length (mm):
15.5	
	Max. Diameter (mm):
13	
	Overall Length (mm):
62	

Hardware & Interface Connectivity

	Type of Drive:
English Micrometer	

Regulatory Compliance

	RoHS 2015:
Exempt	
	Certificate of Conformance:
View	
	REACH 241:
Contains SVHC(s)	

Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
 - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential.
- Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

Technical Information

