

0.50" Travel, 0.001" Grad, Micrometer Drive Mech



Drive Mechanisms

Stock **#58-660** [CONTACT US](#)

-

1

+

A\$243.20

ADD TO CART

Qty 1+

A\$243.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Drive:
English Micrometer

Type:
English

Travel (inches):
0.5

Graduation (inches):
0.001

Manufacturer:
PARKER-HANNIFIN

Stem Diameter (mm): 9.5
Stem/Spindle: Plain/Flat
Stem Length (mm): 9.5
Spindle Diameter (mm): 6.6 (0.26")
Min. Spindle Length (mm): 6.35 (0.25")
Max. Diameter (mm): 13.7 (0.54")
Overall Length (mm): 60.5 (2.38")

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View