

TECHSPEC<sup>®</sup> 0.5mm, Uncoated, N-BK7 Right Angle Prism



N-BK7 Right Angle Prisms

Stock #45-946 3-5 DAYS

-

1

+

A\$158.40

ADD TO CART

Qty 1-5

A\$158.40

Qty 6+

A\$126.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating:  
Uncoated

Substrate: ☐  
[N-BK7](#)

Surface Quality:  
20-10

|                                             |
|---------------------------------------------|
| <b>Type:</b><br>Right Angle Prism           |
| <b>Dimensional Tolerance (mm):</b><br>±0.02 |
| <b>Angle Tolerance (arcmin):</b><br>±2      |
| <b>Bevel:</b><br>Protective bevel as needed |
| <b>Length of Hypotenuse (mm):</b><br>0.70   |
| <b>Length of Legs (mm):</b><br>0.50         |
| <b>Image Orientation:</b><br>Left-Handed    |
| <b>Ray Deviation (°):</b><br>90             |
| <b>Wavelength Range (nm):</b><br>350 - 2200 |
| <b>Surface Flatness (P-V):</b><br>λ/4       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>Reach 191:</b><br><a href="#">Compliant</a>             |
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |