

0.5" Travel, Eng Micrometer, Solid-Top Ball Bearing Stage



32mm/1.25" Center drive stage and its X-Y-Z configuration

Stock **#38-958** 3-5 DAYS



1



A\$667.20

ADD TO CART

Qty 1+

A\$667.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Ball Bearing

Type of Drive:
English Micrometer

Drive Orientation:
Center Drive

Type:
English

Stage Size (mm): 31.8 x 32.5
Travel (inches): 0.5
Construction: Aluminium Stage
Graduation (inches): 0.001
Height (inches): 0.50
Height (mm): 12.7
Load Capacity, Normal (lbs): 6
Note: Solid Top
Stage Size (inches): 1.25 x 1.28
Straight Line Accuracy (inches): 0.00008/inch of travel
Weight (lbs): 0.16
Thrust Capacity, T_a (lbs): 10
Thrust Capacity, T_b (lbs): 3

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View