

0.5" x 6.00", 0.25" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock #46-107 **20+ In Stock**

A\$84⁰⁰

ADD TO CART

Volume Pricing

Qty 1-10	A\$84.80 each
Qty 11-49	A\$76.80 each
Need More?	Request Quote

Product Downloads

General

Fresnel Lens **Type:**

Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

Dimensions (inches):

0.5 x 6.0

Dimensions (mm):

12.7 x 152.4

Effective Size (inches):

0.25 x 6.0

Thickness Tolerance (inches):

±0.020

Optical Properties

Effective Focal Length EFL (mm):

6.35

Substrate:

Acrylic

Coating:

Uncoated

Wavelength Range (nm):

400 - 1100

Effective Focal Length EFL (inches):

0.25

Groove Density (grooves/inch):

200.00

Index of Refraction (n_d):

1.49

Transmission (%):

85 (Typical)

Environmental & Durability Factors

Operating Temperature (°C):

80 (Maximum)

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 242:

[Compliant](#)

Product Details

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

Technical Information

