

**TECHSPEC® 0.6 OD 12.5mm Diameter UV-VIS ND Filter**



Stock **#49-063** 3-5 DAYS

-

1

+

**A\$144.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| A\$144.00                     |
| Qty 6+                        |
| A\$115.04                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

Get Product Downloads



**Diameter (mm):**  
12.50 +0.00/-0.20

**Optical Density OD (Average):**  
0.6

**Substrate:** Fused Silica (Corning 7980)

**Coating:**

|                                                     |
|-----------------------------------------------------|
| Metallic Based ND                                   |
| <b>Surface Quality:</b><br>40-20                    |
| <b>Thickness (mm):</b><br>1.50                      |
| <b>Thickness Tolerance (mm):</b><br>±0.10           |
| <b>Transmission (%):</b><br>25.00                   |
| <b>Type:</b><br>Neutral Density Filter              |
| <b>Blocking Wavelength Range (nm):</b><br>250 - 700 |
| <b>Clear Aperture (%):</b><br>80.00                 |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4           |
| <b>Optical Density Tolerance (%):</b><br>±10        |
| <b>Parallelism (arcsec):</b><br><5                  |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |