

0.6 OD M22.5 x 0.50, Mounted Absorptive ND Filter



Stock **#59-167** 3-5 DAYS

-

1

+

A\$61.60

ADD TO CART

Qty 1-9

A\$61.60

Qty 10+

A\$60.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
18.5

Filter Thread:
M22.5 x 0.50

Substrate: ☐
ND Filter Glass

Thickness with Mount (mm): 4.5
Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 24.0 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View
