

0.6 OD M37.0 x 0.75, Mounted Absorptive ND Filter



Stock #59-170 CLEARANCE 3-5 DAYS

⊖ 1 ⊕ **A\$68.80**

ADD TO CART

Qty 1-9

A\$68.80

Qty 10+

A\$64.96

Volume Pricing

[Request Quote](#)

Get Product Downloads

Optical Density OD (Average):

0.6

Clear Aperture CA (mm):

31.9

Filter Thread:

M37 x0.75

Substrate:

ND Filter Glass

Thickness with Mount (mm):
4.50

Surface Quality:
80-50

Transmission (%):
25

Type:
Mounted Imaging Filter

Blocking Wavelength Range (nm):
400 - 700

Mount Thickness (mm):
5.2 ±0.3

Note:
AR Coating: MgF₂

Coating Specification:
R_{avg} ≤ 1.75% @ 400 - 700nm

Mount Diameter (mm):
39.0 ±0.3

Mount Thickness Including Threads (mm):
6.5

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)
