

0.6 OD M43 x 0.75, Machine Vision Absorptive ND Filter



Stock #21-700 3-5 DAYS

- 1 + **A\$108.00**

ADD TO CART

Qty 1-9
A\$108.00
Qty 10+
A\$103.68
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
38.00

Filter Thread:
M43 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 25.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
